




所用物料均符合ROHS标准

标“*”为重点检验尺寸

PO(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
015	16.33	24.99	30.81	19.28
026	24.66	33.32	39.14	27.51
044	38.38	47.04	53.04	41.28



NOTICE :

1. ELECTRIC:

DIELECTRIC RATING: 300V

CONTACT CURRENT RATING: 3AMP

CONTACT RESISTANCE: 15mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN. AT 500V DC

DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE

OPERATION TEMPERATURE: -55°C ~ 125°C

2. MATERIAL:

INSULATOR: PBT+30% G. F (UL94V-0)

CONTACT: COPPER ALLOY

CONTACT PLATED: GOLD FLASH OVER NICKEL

SHELL: SPCC


SHELL PLATED: NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE:

XX ±0.38
 XXX ±0.25
 XXXX ±0.13

X* ±5° X.X* ±2°



UNIT: mm [inch]

SCALE: 1:1 A版

DRAWN BY :

DATE :

PART NAME:

2011.01.05

HDB XP 母 焊线式传统铆合QW

CHECKED BY :

DATE :

DRAW NO.

2011.01.05

HDD-M- **P-HX-GK

APPROVED BY :

DATE :

REMARK

2014.11.05

MOLD NO.