




"*" Pivot Dimension

RoHS Component



NOTICE :



1. ELECTRIC:

- DIELECTRIC RATING: 300V
- CONTACT CURRENT RATING: 3AMP
- CONTACT RESISTANCE: 15mΩ MAX.
- INSULATION RESISTANCE: 1000MΩ MIN. AT 500V DC
- DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE
- OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

- INSULATOR: PBT+30% G. F(UL94V-0)
- CONTACT: COPPER ALLOY
- CONTACT PLATED: GOLD FIASH OVER NICKEL
- SHELL: SPCC
- SHELL PLATED: NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X° ±5° XX° ±2°	DRAWN BY : _____	DATE : _____	PART NAME: QW HDB 78 公 焊线式传统铆合	
	CHECKED BY: _____	DATE : _____	DRAW NO. HDD-G-78P-HX-GK	PART NO. _____
 	APPROVED BY: _____	DATE : _____	REMARK _____	
UNIT: mm [inch]	SCALE: 1:1	SIZE: A4	MOLD NO. _____	