




“*” Pivot Dimension

RoHS Component



NOTICE :

1. ELECTRIC:

- DIELECTRIC RATING: 300V
- CONTACT CURRENT RATING: 3AMP
- CONTACT RESISTANCE: 15mΩ MAX.
- INSULATION RESISTANCE: 1000MΩ MIN. AT 500V DC
- DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE
- OPERATION TEMPERATURE: -55°C ~125°C

2. MATERIAL:

- INSULATOR: PBT+30% G. F (UL94V-0)
- CONTACT: COPPER ALLOY
- CONTACT PLATED: GOLD FIASH OVER NICKEL
- SHELL: SPCC
- SHELL PLATED: NICKEL/TIN

浙江创都电子科技有限公司

| | | | | |
|---|------------------------------|-------------------------------|---|------------------------|
| TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X.* ±5° X.X* ±1° | DRAWN BY : _____ | DATE : 2009. 12. 16 | PART NAME: HDB 62 母 焊线式传统铆合OW | |
| | CHECKED BY: _____ | DATE : 2014. 11. 05 | DRAW NO. _____ | HDD-M-62P-HX-GK |
| | APPROVED BY: _____ | DATE : 2014. 11. 05 | REMARK _____ | |
| UNIT: mm [inch] SCALE:1:1 A版 | | | MOLD NO. _____ | |