





"\*" Pivot Dimension

RoHS Component



PCB LAYOUT

NOTICE :

1. ELECTRIC:

DIELECTRIC RATING: 300V

CONTACT CURRENT RATING: 5AMP

CONTACT RESISTANCE: 15mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN. at 500V DC

DIELECTRIC STRENGTH: 500V AC RMS for 1Minute

OPERATION TEMPERATURE: -55C° ~125C°

2. MATERIAL:

INSULATOR: PBT+30% G. F (UL94V-0)

CONTACT: COPPER ALLOY

CONTACT PLATED: GOLD FIASH OVER NICKEL

SHELL: SPCC

SHELL PLATED: NICKEL/TIN

FORK: COPPER ALLOY NICKEL/TIN

# 浙江创都电子科技有限公司

<b>TOLERANCE:</b> XX ±0.38 XXX ±0.25 XXXX ±0.13 X° ±5°    XX° ±2°	DRAWN BY :	DATE :	PART NAME:	
			2009.11.21	HDP 50P 母直焊板式铆6.0鱼叉 锁4-40UNC*4.8螺丝QH
 UNIT: mm [inch]	CHECKED BY :	DATE :	DRAW NO.	DP-M-50P-7C-YCLS
			2009.11.25	PART NO.
SCALE:1:1    SIZE: A4	APPROVED BY :	DATE :	REMARK	
		2009.11.25	MOLD NO.	