


HSF



RoHS



Specifications:

Current Rating: 1.5A Max

Contact Resistance: 30 milliohms MAX

Dielectric Withstanding Voltage:

500V AC AT Sea Level

Insulation Resistance: 1000 Megohms MIN

Housing:

Temperature Thermoplastics, PBT UL 94V-0

Contact:

Copper Alloy T=0.25mm Plated Gold in Mating Area;

Tin On Solder Tails

Shell: Iron T=0.30mm Nickel/Plating

Ordering Code:

UAFR03 - X - X - X - X - X - X

① ② ③ ④ ⑤ ⑥ ⑦

① Series No:

② Shell Material:

B: Brass I: Iron

S: stainless steel

③ Insulator Material:

P: PBT+30%GF L: LCP

④ Contact Material:

B: Brass P: phosphor copper

⑤ Contact Plating

G0: Gold flash

G1: 3u" Gold

G2: 5u" Gold

G3: 10u" Gold

G4: 15u" Gold

G5: 30u" Gold

⑥ Color Insulator

A: White B: Black

⑦ Packing

A: Tray B: Bag

C: Tube D: Tape & Reel

Unless Otherwise specified tolerance

X. ±0.35

X. XX: ±0.20

X. X: ±0.25

X. XXX: ±0.15

SCALE:

UNIT:

As Shown

mm

DRAW

DATE

YIN CHAO

2026/4/3

CHECK

DATE

BobYang

2026/4/3



3rd ANGLE PROJECTION



ANTENK ELECTRONICS CO., LTD

Http://www.antenk.com

E-mail:sales@antenk.com

TITLE:

USB A Type Receptacle Angle Upright DIP

DRAWING NO:

UAFR03-IPBG0AA

PRODUCT NO:

UAFR03-IPBG0AA

D

D

REV	DESCRIPTION	DATE
1		
2		
3		
4		
5		
6		
7		
8		