




所用物料均符合ROHS标准

标“*”为重点检验尺寸

PO(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
015	16.92	24.99	30.81	19.28
026	25.25	33.32	39.14	27.51
044	38.96	47.04	53.04	41.28



NOTICE :

- ELECTRICE:
 - DIELECTRIC RATING: 300V
 - CONTACT CURRENT RATING: 3AMP
 - CONTACT RESISTANCE: 15mΩ MAX.
 - INSULATION RESISTANCE: 1000MΩ MIN. AT 500V DC
 - DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE
 - OPERATION TEMPERATURE: -55°C ~125°C
- MATERIAL:
 - INSULATOR: PBT+30% G. F(UL94V-0)
 - CONTACT: COPPER ALLOY
 - CONTACT PLATED: GOLD FIASH OVER NICKEL
 - SHELL: SPCC
 - SHELL PLATED: NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X.* ±5° X.X* ±2°	DRAWN BY : _____	DATE : 2011.01.05	PART NAME: HDB XP 公 焊线式传统铆合QW	
	CHECKED BY: _____	DATE : 2011.01.05	DRAW NO. HDD-G-**P-HX-GK	PART NO. _____
UNIT: mm [inch] _____	APPROVED BY: _____	DATE : 2014.11.05	REMARK _____	
SCALE:1:1 A版			MOLD NO. _____	_____