




所用物料均符合ROHS标准

标“\*”为重点检验尺寸

PO(XXX)	A ±0.25	B ±0.13	C ±0.38	D ±0.25
015	16.92	24.99	30.81	19.28
026	25.25	33.32	39.14	27.51
044	38.96	47.04	53.04	41.28



NOTICE :

1. ELECTRICE:

DIELECTRIC RATING: 300V

CONTACT CURRENT RATING: 3AMP

CONTACT RESISTANCE: 15mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN. AT 500V DC

DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE

OPERATION TEMPERATURE: -55°C ~125°C

2. MATERIAL:

INSULATOR: PBT+30% G. F(UL94V-0)

CONTACT: COPPER ALLOY

CONTACT PLATED: GOLD FIASH OVER NICKEL

SHELL: SPCC

SHELL PLATED: NICKEL/TIN

# 浙江创都电子科技有限公司

<b>TOLERANCE:</b> XX ±0.38 XXX ±0.25 XXXX ±0.13 X.* ±5°    X.X* ±2°	<b>DRAWN BY :</b> _____	<b>DATE :</b> 2011.01.05	<b>PART NAME:</b> HDB XP 公 焊线式传统铆合QW	
	<b>CHECKED BY:</b> _____	<b>DATE :</b> 2011.01.05	<b>DRAW NO.</b> HDD-G-**P-HX-GK	<b>PART NO.</b> _____
Ⓢ    Ⓢ	<b>APPROVED BY:</b> _____	<b>DATE :</b> 2014.11.05	<b>REMARK</b> _____	
<b>UNIT: mm [inch]</b> SCALE:1:1    A版			<b>MOLD NO.</b> _____	