


SCHEMATIC



PIN	φ2.0	φ2.35	φ2.5
APPD.			

SPECIFICATION

1. Rating : DC 24V 5A;
2. Contact resistance: $\leq 50m\Omega$;
3. Insulation resistance: $\geq 100M\Omega$ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-25N;
6. life test: 5,000 cycles.

5	HOUSING	1	PA66	
4	HOUSING	1	PA66	
3	PIN	1	BRASS	Sn-Plating
2	AXIS SUPPORT	1	BRASS	Ni-Plating
1	SPRING	1	phosphor bronze	Sn-Plating
NO.	DESCRIPTION	QTY	MATERIAL	PLATING
UNIT:MM	TYPE:	MODEL NO:	PAPER NO:	PAGE 1 OF 1
	DC JACK	DC-083C-5A-2.0-S	± 0.3	1
DESIGNER			TOLERANCE	SCALE
CHECK			ANGLES	VER
APPROVED			±2'	1:1
BY:				

浙江创都电子科技有限公司