



REV.	DESCRIPTION	ECN NO.	NAME	DATE

- Specifications:
- Electrical:
- Current Rating
1.5A/contact terminal
 - Voltage Rating
30V DC
 - Contact Resistance
30 milliohms MAX
 - Dielectric Withstanding Voitage:
500 V AC AT Sea Level
 - Insulation Resistance:
1000MEGA ohms MIN
- Mechanical:
- Connector Mate and Unmate Force
Mate force:3.75kgf(MAX)
Unmate force:1.02kgf(MIN)
 - Terminal Retention:1.2kgf(MIN)
- Material:
- Housing:Hing Temperature
Thermoplastics,UI 94V-0 PBT White
 - Contact:Copper Alloy C2680
 - Shell: Copper Alloy C2680/SPCC
- Finish:
- Contact: Plated Gold in Mating Area;
Tin On Solder Talls.
 - Shell: Nickel Plating

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x.° ±3.0° x.x° ±2.0° x.xx°		TITLE: Type-B 弯插90度 B型母座 铁壳				
		DWG. NO.: USB-B10-WC		CHECKED: MAX		
UNIT: mm		SCALE: none		DRAWN: ELLA		
SHEET: 1 of 1		DWG. SIZE: A4		APPROVED: WILL		