




"*" Pivot Dimension



RoHS Component



NOTICE :

- ELECTRICE:
 - DIELECTRIC RATING: 300V
 - CONTACT CURRENT RATING: 5AMP
 - CONTACT RESISTANCE: 15mΩ MAX.
 - INSULATION RESISTANCE: 1000MΩ MIN. at 500V DC
 - DIELECTRIC STRENGTH: 500V AC RMS for 1Minute
 - OPERATION TEMPERATURE: -55°C ~125°C
- MATERIAL:
 - INSULATOR: PBT+30% G. F(UL94V-0)
 - CONTACT: COPPER ALLOY
 - CONTACT PLATED:GOLD FIASH OVER NICKEL
 - SHELL: SPCC
 - SHELLPLATED:NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X° ±5° XX° ±2°	DRAWN BY :	DATE :	PART NAME:	
			2009.11.21	HDB 50P 母焊线式传统铆合GW
 	CHECKED BY:	DATE :	DRAW NO.	DB-M-50P-HX-GK
			2009.11.25	PART NO.
UNIT: mm [inch]	APPROVED BY:	DATE :	REMARK	
SCALE:1:1 SIZE: A4		2009.11.25	MOLD NO.	