




“*” Pivot Dimension

RoHS Component



NOTICE :

- ELECTRICE:
 - DIELECTRIC RATING: 300V
 - CONTACT CURRENT RATING: 3AMP
 - CONTACT RESISTANCE: 15mΩ MAX.
 - INSULATION RESISTANCE: 1000MΩ MIN. AT 500V DC
 - DIELECTRIC STRENGTH: 500V AC RMS FOR 1MINUTE
 - OPERATION TEMPERATURE: -55C° ~125C°
- MATERIAL:
 - INSULATOR: PBT+30% G. F(UL94V-0)
 - CONTACT: COPPER ALLOY
 - CONTACT PLATED:GOLD FIASH OVER NICKEL
 - SHELL: SPCC
 - SHELL PLATED:NICKEL/TIN

浙江创都电子科技有限公司

TOLERANCE: XX ±0.38 XXX ±0.25 XXXX ±0.13 X.* ±5° X.X* ±1°	DRAWN BY : _____	DATE : 2009.12.16	PART NAME: HDB 62 公 焊线式传统铆合0W	
	UNIT: mm [inch] SCALE:1:1 A版	CHECKED BY: _____	DATE : 2014.11.05	DRAW NO. HDD-G-62P-HX-GK
	APPROVED BY: _____	DATE : 2014.11.05	REMARK _____	
			MOLD NO. _____	