



REV.	DESCRIPTION	ECN NO.	NAME	DATE



1
2
3
4
5



SPECIFICATIONS
 Current Rating: 1.0 Amps
 Withstanding Voltage: AC 500V
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Operation Temperature: -40°to+105°
 Insulator Material: Polyester(UL94V-0)
 Contact Material: Brass
 Standard: PA6T
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
PH1.27-01-01PZD	1	0.00	1.27
PH1.27-01-02PZD	2	1.27	2.54
PH1.27-01-03PZD	3	2.54	3.81
PH1.27-01-04PZD	4	3.81	5.08
PH1.27-01-05PZD	5	5.08	6.35
PH1.27-01-06PZD	6	6.35	7.62
PH1.27-01-07PZD	7	7.62	8.89
PH1.27-01-08PZD	8	8.89	10.16
PH1.27-01-09PZD	9	10.16	11.43
.....
PH1.27-01-50PZD	50	(PIN-1)x1.27	(PIN)x1.27

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x° ±5° x.x° ±1° x.xx° ±0.5°		TITLE: 1.27PH H1.0 1xnPin 180度 W2.0 PC2.3 PA3.9 PB1.0 L7.2 6T 0.4#				
		DWG. NO.: A127UP-ZD04P-PA3.9		CHECKED: MAX		
		PART NO.: A127UP-ZD04P-PA3.9		DRAWN: ELLA		
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	