



REV.	DESCRIPTION	ECN NO.	NAME	DATE


1  
2  
3  
4  
5



**SPECIFICATIONS**  
 Current Rating: 1.0 Amps  
 Withstanding Voltage: AC 500V  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Operation Temperature: -40°to+105°  
 Insulator Material: Polyester(UL94V-0)  
 Contact Material: Brass  
 Standard: PA6T  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for30-60seconds  
 (260°C for5seconds)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
PH1.27-01-01PZD	1	0.00	1.27
PH1.27-01-02PZD	2	1.27	2.54
PH1.27-01-03PZD	3	2.54	3.81
PH1.27-01-04PZD	4	3.81	5.08
PH1.27-01-05PZD	5	5.08	6.35
PH1.27-01-06PZD	6	6.35	7.62
PH1.27-01-07PZD	7	7.62	8.89
PH1.27-01-08PZD	8	8.89	10.16
PH1.27-01-09PZD	9	10.16	11.43
.....	.....	.....	.....
PH1.27-01-50PZD	50	(PIN-1)x1.27	(PIN)x1.27

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. TOL.	TITLE: 1.27PH H1.0 1xnPin 180度 W2.0 PC2.3 PA3.9 PB1.0 L7.2 6T 0.4#			
x. ±0.30	DWG. NO.:	A127UP-ZD04P-PC2.3		CHECKED: MAX
x.x ±0.20	PART NO.:	A127UP-ZD04P-PC2.3		DRAWN: ELLA
x.xx ±0.10	UNIT:	mm	SCALE:	none
GENERAL ANGLE:	SHEET:	1 of 1	DWG. SIZE:	A4
x' ±5'	LAYER:	bxconn	APPROVED:	WILL
x.x' ±1'				
x.xxx ±0.5'				

