



REV.	DESCRIPTION	ECN NO.	NAME	DATE

Part No	Pin	A	B	C
FC-05F4P11H42	4	1.50	2.60	5.05
FC-05F5P11H42	5	2.00	3.10	5.55
FC-05F6P11H42	6	2.50	3.60	6.05
FC-05F7P11H42	7	3.00	4.10	6.55
FC-05F8P11H42	8	3.50	4.60	7.05
FC-05F9P11H42	9	4.00	5.10	7.55
FC-05F10P11H42	10	4.50	5.60	8.05
FC-05F11P11H42	11	5.00	6.10	8.55
FC-05F12P11H42	12	5.50	6.60	9.05
FC-05F13P11H42	13	6.00	7.10	9.55
FC-05F14P11H42	14	6.50	7.60	10.05
FC-05F15P11H42	15	7.00	8.10	10.55
.....
FC-05F60P11H42	60	(60-1)*0.5	(60+1)*0.5+0.1	(60+6)*0.5+0.05

序号	品名	材质
1	0.5C胶芯	LCP UL94V-0 本色
2	0.5C端子	磷青铜/表面镀锡
3	0.5C焊片	磷青铜/表面镀锡

- 技术指标:
1. 额定电流: 0.5A
 2. 温度范围: -40~85℃
 3. 额定电压: 50V, AC/DC (等效)
 4. 接触电阻: ≤0.03Ω
 5. 绝缘电阻: ≥500MΩ

GENERAL TOLERANCE: DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

DIM. TOL. ±0.15
 x.x ±0.10
 x.xx ±0.05
 GENERAL ANGLE: ±1°

TITLE: FPC 0.5C 无锁 立贴

DWG. NO.: FC-05FXP11H42 CHECKED: MAX

PART NO.: FC-05FXP11H42 DRAWN: ELLA

UNIT: mm SCALE: none SHEET: 1 of 1 DWG. SIZE: A4 LAYER: bxconn APPROVED: WILL

