





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

P / N	PIN	DIM. A	DIM. B
HMT-PZ254R-2X01P-C30	2*1	0.00	2.54
HMT-PZ254R-2X02P-C30	2*2	2.54	5.08
HMT-PZ254R-2X03P-C30	2*3	5.08	7.62
HMT-PZ254R-2X04P-C30	2*4	7.62	10.16
HMT-PZ254R-2X05P-C30	2*5	10.16	12.70
HMT-PZ254R-2X06P-C30	2*6	12.70	15.24
HMT-PZ254R-2X07P-C30	2*7	15.24	17.78
HMT-PZ254R-2X08P-C30	2*8	17.78	20.32
HMT-PZ254R-2X09P-C30	2*9	20.32	22.86
.....			
HMT-PZ254R-2X40P-C30	2*40	(PIN-1) X 2.54	(PIN) X 2.54

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.30	X.° ± 5°	PART NO.	TITLE:	
.X ± 0.20	.X° ± 1°	HMT-PZ254R-2XNP-C30	2.54PH H2.5 2xnPin 90° PC3.0 PA6.0 PB6.9 L13.8/18.8 6T 等四角	
.XX ± 0.10	.XX° ± 0.5°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
				N:A
				1/1