





P / N	PIN	DIM. A	DIM. B
HMT-PZ254WV-2X01H-C 60	2*1	0.00	2.54
HMT-PZ254WV-2X02H-C 60	2*2	2.54	5.08
HMT-PZ254WV-2X03H-C 60	2*3	5.08	7.62
HMT-PZ254WV-2X04H-C 60	2*4	7.62	10.16
HMT-PZ254WV-2X05H-C 60	2*5	10.16	12.70
HMT-PZ254WV-2X06H-C 60	2*6	12.70	15.24
HMT-PZ254WV-2X07H-C 60	2*7	15.24	17.78
HMT-PZ254WV-2X08H-C 60	2*8	17.78	20.32
HMT-PZ254WV-2X09H-C 60	2*9	20.32	22.86
.....			
HMT-PZ254WV-2X40H-C 60	2*40	(PIN-1) X2.54	(PIN) X2.54

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.30	X. $^{\circ} \pm 5^{\circ}$	PART NO.	TITLE:	
.X ± 0.20	.X $^{\circ} \pm 1^{\circ}$	HMT-PZ254WV-2XNH-C60	2.54PH H2.5 2xNPin 180度 PC3.0 PA6.0 PB2.5 L11.5 6T	
.XX ± 0.10	.XX $^{\circ} \pm 0.5^{\circ}$	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
				N:A
				1/1