





SPECIFICATIONS

Current Rating:1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40° to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Brass
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp: 240° C for30-60seconds
(260° C for5seconds)

P/N	PIN	DIM. A	DIM. B
HMT-PZ127VS-01P-C55	2*1	0.00	1.27
HMT-PZ127VS-02P-C55	2*2	1.27	2.54
HMT-PZ127VS-03P-C55	2*3	2.54	3.81
HMT-PZ127VS-04P-C55	2*4	3.81	5.08
HMT-PZ127VS-05P-C55	2*5	5.08	6.35
HMT-PZ127VS-06P-C55	2*6	6.35	7.62
HMT-PZ127VS-07P-C55	2*7	7.62	8.89
HMT-PZ127VS-08P-C55	2*8	8.89	10.16
HMT-PZ127VS-09P-C55	2*9	10.16	11.43
.....			
HMT-PZ127VS-50P-C55	2*50	(PIN-1)x1.27	(PIN)x1.27

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTconn Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.30	X.°±5°	PART NO.	TITLE:	
.X±0.25	.X°±1°	HMT-PZ127VS-NP-C55	1.27PH H1.0 2xnPin SMT	
.XX±0.20	.XX°±0.5°	DESIGN: James	CUSTOMER	W3.4 PC5.5 PA4.0 PB1.5 L7.2 6T
MANUFACTURE DWG		CHED: Talen		SIZE
		APPD: Sophia		UNITS
				A4
				MM
				SCALE
				N:A
				SHEET
				1/1