






**SPECIFICATIONS**

Current Rating:3Amps  
 Insulation Resistance:1000MΩ Min  
 Contact Resistance:20mΩ Max  
 Withstanding Voltage:AC 1000V  
 Operation Temperature:-40° to +105°  
 Contact Material:Brass  
 Insulator Material: Polyester(UL 94V-0)  
 Contact plating:Gold Flash  
 Standard:PA6T  
 Max. Processing Temp:240° C for30-60seconds  
 (260° Cfor10seconds)



RECOMMEND P. C. B LAYOUT  
 PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM. A	DIM. B
HMT-JN254-2*03Z	2*3	5.08	7.62
HMT-JN254-2*04Z	2*4	7.62	10.16
HMT-JN254-2*05Z	2*5	10.16	12.70
HMT-JN254-2*06Z	2*6	12.70	15.24
HMT-JN254-2*07Z	2*7	15.24	17.78
HMT-JN254-2*08Z	2*8	17.78	20.32
HMT-JN254-2*09Z	2*9	20.32	22.86
HMT-JN254-2*10Z	2*10	22.86	25.40
HMT-JN254-2*12Z	2*12	27.94	30.48
HMT-JN254-2*13Z	2*13	30.48	33.02
HMT-JN254-2*14Z	2*14	33.02	35.56
HMT-JN254-2*15Z	2*15	35.56	38.10
HMT-JN254-2*16Z	2*16	38.10	40.64
HMT-JN254-2*17Z	2*17	40.64	43.18
HMT-JN254-2*18Z	2*18	43.18	45.72
HMT-JN254-2*20Z	2*20	48.26	50.80
HMT-JN254-2*22Z	2*22	53.34	55.88
HMT-JN254-2*25Z	2*25	60.96	63.50
HMT-JN254-2*30Z	2*30	73.66	76.20
HMT-JN254-2*32Z	2*32	78.74	81.28

GENERAL TOLERANCES UNLESS SPECIFIED		 <b>深圳市华明通电子有限公司</b> Shenzhen Huamingtong Electronics Co., Ltd	
X.±0.30	X.°±5°	PART NO. HMT-JN254-2*NZ	TITLE: 2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T
.X±0.25	.X°±1°	DESIGN: James	CUSTOMER
.XX±0.20	.XX°±0.5°	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1