





P / N	PIN	DIM. A	DIM. B
HMT-PM127-2*01S-H43	1	0.00	1.27
HMT-PM127-2*02S-H43	2	1.27	2.54
HMT-PM127-2*03S-H43	3	2.54	3.81
HMT-PM127-2*04S-H43	4	3.81	5.08
HMT-PM127-2*05S-H43	5	5.08	6.35
HMT-PM127-2*06S-H43	6	6.35	7.62
HMT-PM127-2*07S-H43	7	7.62	8.89
HMT-PM127-2*08S-H43	8	8.89	10.16
HMT-PM127-2*09S-H43	9	10.16	11.43
.....			
HMT-PM127-2*50S-H43	50	(PIN-1) x 1.27	(PIN) x 1.27

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.30	X.° $\pm 5^\circ$	PART NO. HMT-PM127-2*NS-H43	TITLE: 1.27FH H4.3 2xNPin SMT U型 PC4.8 PB4.6 6T	
.X ± 0.20	.X° $\pm 1^\circ$			
.XX ± 0.10	.XX° $\pm 0.5^\circ$	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		A4
		APPD: Sophia		UNITS
				MM
			SCALE	SHEET
			N:A	1/1