





SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

P / N	PIN	DIM. A	DIM. B
HMT-PM254-2*01W-H85	1	0.00	2.54
HMT-PM254-2*02W-H85	2	2.54	5.08
HMT-PM254-2*03W-H85	3	5.08	7.62
HMT-PM254-2*04W-H85	4	7.62	10.16
HMT-PM254-2*05W-H85	5	10.16	12.70
HMT-PM254-2*06W-H85	6	12.70	15.24
HMT-PM254-2*07W-H85	7	15.24	17.78
HMT-PM254-2*08W-H85	8	17.78	20.32
HMT-PM254-2*09W-H85	9	20.32	22.86
.....			
HMT-PM254-2*40W-H85	40	(PIN-1) X 2.54	(PIN) X 2.54

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.50	X.° $\pm 5^\circ$	PART NO.	TITLE: 2.54FH H8.5 2xnPin	
.X ± 0.20	.X° $\pm 2^\circ$	HMT-PM254-2*NW-H85	90度 Y型 PC3.2 PB12.7 6T	
.XX ± 0.10	.XX° $\pm 1^\circ$	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
				N:A
				1/1