





P / N	PIN	DIM. A	DIM. B
HMT-PZ127WV-01H-C18	1	0.00	1.27
HMT-PZ127WV-02H-C18	2	1.27	2.54
HMT-PZ127WV-03H-C18	3	2.54	3.81
HMT-PZ127WV-04H-C18	4	3.81	5.08
HMT-PZ127WV-05H-C18	5	5.08	6.35
HMT-PZ127WV-06H-C18	6	6.35	7.62
HMT-PZ127WV-07H-C18	7	7.62	8.89
HMT-PZ127WV-08H-C18	8	8.89	10.16
HMT-PZ127WV-09H-C18	9	10.16	11.43
.....			
HMT-PZ127WV-50H-C18	50	(PIN-1) x 1.27	(PIN) x 1.27

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.30	X.° $\pm 5^\circ$	PART NO.	TITLE:	
.X ± 0.20	.X° $\pm 1^\circ$	HMT-PZ127WV-NH-C18	1.27PH H1.0 1x nPin 180度 W2.0	
.XX ± 0.10	.XX° $\pm 0.5^\circ$	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
			N:A	1/1