



REV.	DESCRIPTION	ECN NO.	NAME	DATE

Part No	Pin	A	B	c
FC-05C4P11H20L	4	1.50	2.60	7.60
FC-05C5P11H20L	5	2.00	3.10	8.10
FC-05C6P11H20L	6	2.50	3.60	8.60
FC-05C7P11H20L	7	3.00	4.10	9.10
FC-05C8P11H20L	8	3.50	4.60	9.60
FC-05C9P11H20L	9	4.00	5.10	10.10
FC-05C10P11H20L	10	4.50	5.60	10.60
FC-05C11P11H20L	11	5.00	6.10	11.10
FC-05C12P11H20L	12	5.50	6.60	11.60
FC-05C13P11H20L	13	6.00	7.10	12.10
FC-05C14P11H20L	14	6.50	7.60	12.60
FC-05C15P11H20L	15	7.00	8.10	13.10
.....	....	...	.....	.....
FC-05C60P11H20L	60	(60-1)*0.5	(60+1)*0.5+0.1	(60+11)*0.5+0.1

序号	品名	材质
1	端子	磷青铜/表面镀锡
2	焊片	黄铜/表面镀锡
3	基座	LCP UL94V-0 本色
4	锁条	LCP UL94V-0 黑色

- 技术指标:
1. 额定电流: 0.5A
  2. 温度范围: -40~85℃
  3. 额定电压: 50V, AC/DC (等效)
  4. 接触电阻: ≤0.03Ω
  5. 绝缘电阻: ≥500MΩ

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	
DIM. x. ±0.15 x.x ±0.10 x.xx ±0.05 GENERAL ANGLE: ±10°	TITLE: 0.5-A全包拉拔立式(正位)	
	DWG. NO.: FC-05CXP11H20L	CHECKED: MAX
	PART NO.: FC-05CXP11H20L	DRAWN: ELLA
	UNIT: mm	SCALE: none
	DWG. SIZE: A4	LAYER: bxconn
	APPROVED: WILL	

BXCONN<sup>®</sup>

