




SPECIFICATIONS


Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)



P/N	PIN	DIM. A	DIM. B
HMT-PZ254V-1P-C60	1	0.00	2.54
HMT-PZ254V-2P-C60	2	2.54	5.08
HMT-PZ254V-3P-C60	3	5.08	7.62
HMT-PZ254V-4P-C60	4	7.62	10.16
HMT-PZ254V-5P-C60	5	10.16	12.70
HMT-PZ254V-6P-C60	6	12.70	15.24
HMT-PZ254V-7P-C60	7	15.24	17.78
HMT-PZ254V-8P-C60	8	17.78	20.32
HMT-PZ254V-9P-C60	9	20.32	22.86
.....			
HMT-PZ254V-40P-C60	40	(PIN-1) X 2.54	(PIN) X 2.54



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X. ± 0.30	X.° $\pm 5^\circ$	PART NO. HMT-PZ254V-NP-C60	TITLE: 2.54PH H2.5 1xnPin 180度 PC3.0 PA6.0 PB2.5 L11.5 6T	
.X ± 0.20	.X° $\pm 1^\circ$			
.XX ± 0.10	.XX° $\pm 0.5^\circ$	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
				N:A
				1/1