

1

2

3

4

5

6

REV.

ECN NO OR DESCRIPTION

REVISED

DATE

RoHS Compliant

ON

1

2

3

4

5

6

7

8

DIM.A=±0.3

1

2

3

4

5

6

7

8

Circuit Diagram

2.54*(N-1)

7.62

0.97±0.05

[P.C.B.LAYOUT]

1.10

0.60

2.54

5.50±0.1

3.50±0.2

DIM.B

凸柄(T)

1.50

短柄(D)

蓝色凸柄 (GA2)	红色凸柄 (GA2)	PIN No	DIM.A	DIM.B	蓝色短柄 (GA1)	红色短柄 (GA1)
LCK-DSE-02B-GA2	LCK-DSE-02R-GA2	2	6.64	2.54	LCK-DSE-02B-GA1	LCK-DSE-02R-GA1
LCK-DSE-03B-GA2	LCK-DSE-03R-GA2	3	9.18	5.08	LCK-DSE-03B-GA1	LCK-DSE-03R-GA1
LCK-DSE-04B-GA2	LCK-DSE-04R-GA2	4	11.72	7.62	LCK-DSE-04B-GA1	LCK-DSE-04R-GA1
LCK-DSE-05B-GA2	LCK-DSE-05R-GA2	5	14.26	10.16	LCK-DSE-05B-GA1	LCK-DSE-05R-GA1
LCK-DSE-06B-GA2	LCK-DSE-06R-GA2	6	16.80	12.70	LCK-DSE-06B-GA1	LCK-DSE-06R-GA1
LCK-DSE-07B-GA2	LCK-DSE-07R-GA2	7	19.34	15.24	LCK-DSE-07B-GA1	LCK-DSE-07R-GA1
LCK-DSE-08B-GA2	LCK-DSE-08R-GA2	8	21.88	17.78	LCK-DSE-08B-GA1	LCK-DSE-08R-GA1
LCK-DSE-09B-GA2	LCK-DSE-09R-GA2	9	24.42	20.32	LCK-DSE-09B-GA1	LCK-DSE-09R-GA1
LCK-DSE-10B-GA2	LCK-DSE-10R-GA2	10	26.96	22.86	LCK-DSE-10B-GA1	LCK-DSE-10R-GA1

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT

GP

TP

IP

UNLESS OTHERWISE SPECIFIED,TOLERANCE:
X.
X.xx ±0.25
X.xx ±0.15
ANGULAR ±3°

联晟欣连接器 (深圳) 有限公司

Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:
CHECKED		DATE		MULTIFUNCTIONAL SWITCHES
APPROVED		DATE		
PART NO: LCK-DSE-XXX-XXX	REV: 04	SCALE: 1:1	UNIT: mm	
DRAWING NO:	SIZE: A4	SHEET: 1/1		