



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



**SPECIFICATIONS**  
 Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°c to +105°c

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD			
BASIC DIMENSION	TOLERANCE	DSND	H	C	26.02.23
x.x	±0.50	CHKD	L P	J	26.02.23
x.xx	±0.30	APVD	L Z	W	26.02.23
x.xxx	±0.10				
ANGLES	±3°				
		UNIT:mm		SCALE:1:1	SIZE:A4
				SHEET:1/1	
		TITLE:NEEDLE ARRANGEMENT			
		PART NO:FG-PZ2.54-2-NPW-S			