



**SPECIFICATIONS**

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Insulator Material: Polyester (UL 94V-0)  
 Contact plating: Gold Flash  
 Standard: PA6T  
 Max. Processing Temp: 240° C for 30-60 seconds  
 (260° C for 10 seconds)

P/N	PIN	DIM. A	DIM. B
HMT-JN254-2*03W	2*3	5.08	7.62
HMT-JN254-2*04W	2*4	7.62	10.16
HMT-JN254-2*05W	2*5	10.16	12.70
HMT-JN254-2*06W	2*6	12.70	15.24
HMT-JN254-2*07W	2*7	15.24	17.78
HMT-JN254-2*08W	2*8	17.78	20.32
HMT-JN254-2*09W	2*9	20.32	22.86
HMT-JN254-2*10W	2*10	22.86	25.40
HMT-JN254-2*12W	2*12	27.94	30.48
HMT-JN254-2*13W	2*13	30.48	33.02
HMT-JN254-2*14W	2*14	33.02	35.56
HMT-JN254-2*15W	2*15	35.56	38.10
HMT-JN254-2*16W	2*16	38.10	40.64
HMT-JN254-2*17W	2*17	40.64	43.18
HMT-JN254-2*18W	2*18	43.18	45.72
HMT-JN254-2*20W	2*20	48.26	50.80
HMT-JN254-2*22W	2*22	53.34	55.88
HMT-JN254-2*25W	2*25	60.96	63.50
HMT-JN254-2*30W	2*30	73.66	76.20
HMT-JN254-2*32W	2*32	78.74	81.28

GENERAL TOLERANCES UNLESS SPECIFIED		 <b>深圳市华明通电子有限公司</b> Shenzhen Huamingtong Electronics Co., Ltd	
X. ±0.30	X.° ±5°	PART NO. HMT-JN254-2*NW	TITLE: 2.0DC3-nPin H5.7 90度 PC2.8 PB9.3 L10.5/14.5 6T
.X ±0.20	.X° ±1°	DESIGN: James	CUSTOMER
.XX ±0.10	.XX° ±0.5°	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	 SCALE: N:A SHEET: 1/1