





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

P / N	PIN	DIM. A	DIM. B
HMT-PZ254WVT-2x01H-C60R	2*1	0.00	2.54
HMT-PZ254WVT-2x02H-C60R	2*2	2.54	5.08
HMT-PZ254WVT-2x03H-C60R	2*3	5.08	7.62
HMT-PZ254WVT-2x04H-C60R	2*4	7.62	10.16
HMT-PZ254WVT-2x05H-C60R	2*5	10.16	12.70
HMT-PZ254WVT-2x06H-C60R	2*6	12.70	15.24
HMT-PZ254WVT-2x07H-C60R	2*7	15.24	17.78
HMT-PZ254WVT-2x08H-C60R	2*8	17.78	20.32
HMT-PZ254WVT-2x09H-C60R	2*9	20.32	22.86
.....			
HMT-PZ254WVT-2x40H-C60R	2*40	(PIN-1) X 2.54	(PIN) X 2.54

GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd				
X.±0.30	X.°±5°	PART NO. HMT-PZ254WVT-2xNH-C60R		TITLE: 2.54PH H2.5 2xPin SMT PC7.5 PA6.0 PB3.2 L11.0 6T		
.X±0.20	.X°±1°					
.XX±0.10	.XX°±0.5°	DESIGN: James		CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen			A4	MM
		APPD: Sophia			SCALE	SHEET
					N:A	1/1