






**SPECIFICATIONS**

Current Rating:3Amps  
 Insulation Resistance:1000MΩ Min  
 Contact Resistance:20mΩ Max  
 Withstanding Voltage:AC 1000V  
 Operation Temperature:-40° to +105°  
 Contact Material:Brass  
 Insrlator Material: Polyester(UL 94V-0)  
 Contact plating:Gold Flash  
 Standard:PA6T  
 Max. Processing Temp:240° C for30-60seconds  
 (260° Cfor10seconds)



P/N	PIN	DIM. A	DIM. B
HMT-254V-6PJN	2*3	5.08	7.62
HMT-254V-8PJN	2*4	7.62	10.16
HMT-254V-10PJN	2*5	10.16	12.70
HMT-254V-12PJN	2*6	12.70	15.24
HMT-254V-14PJN	2*7	15.24	17.78
HMT-254V-16PJN	2*8	17.78	20.32
HMT-254V-18PJN	2*9	20.32	22.86
HMT-254V-20PJN	2*10	22.86	25.40
HMT-254V-24PJN	2*12	27.94	30.48
HMT-254V-26PJN	2*13	30.48	33.02
HMT-254V-28PJN	2*14	33.02	35.56
HMT-254V-30PJN	2*15	35.56	38.10
HMT-254V-32PJN	2*16	38.10	40.64
HMT-254V-34PJN	2*17	40.64	43.18
HMT-254V-36PJN	2*18	43.18	45.72
HMT-254V-40PJN	2*20	48.26	50.80
HMT-254V-44PJN	2*22	53.34	55.88
HMT-254V-50PJN	2*25	60.96	63.50
HMT-254V-60PJN	2*30	73.66	76.20
HMT-254V-64PJN	2*32	78.74	81.28

GENERAL TOLERANCES UNLESS SPECIFIED		 <b>深圳市华明通电子有限公司</b> Shenzhen Huamingtong Electronics Co., Ltd	
X.±0.30	X.°±5°	PART NO. HMT-254V-NPJN	TITLE: 2.54DC3-NPin H8.9 180度 PC3.2 L11.5 6T
.X±0.25	.X°±1°	DESIGN: James	CUSTOMER
.XX±0.20	.XX°±0.5°	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	 SCALE: N:A SHEET: 1/1