



REV.	DESCRIPTION	ECN NO.	NAME	DATE

Part No	Pin	A	B	C
FC-10F4P11H47	4	3.00	5.10	6.00
FC-10F5P11H47	5	4.00	6.10	7.00
FC-10F6P11H47	6	5.00	7.10	8.00
FC-10F7P11H47	7	6.00	8.10	9.00
FC-10F8P11H47	8	7.00	9.10	10.00
FC-10F9P11H47	9	8.00	10.10	11.00
FC-10F10P11H47	10	9.00	11.10	12.00
FC-10F11P11H47	11	10.00	12.10	13.00
FC-10F12P11H47	12	11.00	13.10	14.00
.....
FC-10F36P11H47	36	(36-1)*1.0	(36+1)*1.0+0.10	38.00

序号	品名	材质
1	基座	LCP UL94V-0 本色
2	端子	磷青铜/表面镀锡

技术指标:

1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: ≤0.03Ω
5. 绝缘电阻: ≥500MΩ

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: FPC 1.0B 黑色 双面接 立式(正位)			
x.	±0.15	DWG. NO.: FC-10FXP11H47		CHECKED: MAX	
x.x	±0.10	PART NO.: FC-10FXP11H47		DRAWN: ELLA	
x.xx	±0.05	UNIT: mm		APPROVED: WILL	
GENERAL ANGLE: ±1°		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn