



REV.	DESCRIPTION	ECN NO.	NAME	DATE

NOTES:
 1.BASE: LCP
 2.PIN: Brass
 3.Solder Tab: Brass

SPECIFICATIONS:
 1.Spacing: 2.0
 2.Voltage Rating: 250V AC DC
 3.Current Rating: 2A AC DC
 4.Insulation Resistance: 800MΩ Min
 5.Contact Resistance: 20mΩ Max
 6.Withstanding voltage: 500V AC 1/Minute
 7.Temperatuer Range: $-25^{\circ} \sim + 85^{\circ}$

Part No	Pin	A	B	C
WF-1F200A2P	2	2.00	8.00	6.80
WF-1F200A3P	3	4.00	10.00	8.80
WF-1F200A4P	4	6.00	12.00	10.80
WF-1F200A5P	5	8.00	14.00	12.80
WF-1F200A6P	6	10.00	16.00	14.80
WF-1F200A7P	7	12.00	18.00	16.80
WF-1F200A8P	8	14.00	20.00	18.80
WF-1F200A9P	9	16.00	22.00	20.80
WF-1F200A10P	10	18.00	24.00	22.80
WF-1F200A11P	11	20.00	26.00	24.80
WF-1F200A12P	12	22.00	28.00	26.80
WF-1F200A13P	13	24.00	30.00	28.80
WF-1F200A14P	14	26.00	32.00	30.80
WF-1F200A15P	15	28.00	34.00	32.80
WF-1F200A16P	16	30.00	36.00	34.80

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	
DIM.	TOL.	TITLE: WAFER 2.00 贴片
x.	± 0.20	DWG. NO.: WF-1F200XP
x.x	± 0.10	CHECKED: MAX
x.xx	± 0.05	PART NO.: WF-1F200XP
GENERAL ANGLE:		DRAWN: ELLA
x. ^o	$\pm 5.0^{\circ}$	APPROVED: WILL
x.x. ^o	$\pm 3.0^{\circ}$	
x.xx. ^o	$\pm 1.0^{\circ}$	
UNIT:	SCALE:	SHEET:
mm	none	1 of 1
	DWG. SIZE:	LAYER:
	A4	bxconn

