



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
ES	00	P	LTR	DESCRIPTION	DATE	DWN APVD
			A	REVISED	25JUN19	T.Q W.H
			A1	REVISED PER ECR-21-114308	8SEPT22	R.S M.S



NOTES;
1. APPLICABLE WIRE SIZE : AWC# 28-26
(UL1571,UL1061)
INSULATION DIA RANGE : $\phi 0.83\text{mm} \sim \phi 1.05\text{mm}$
2. MATERIAL :
HOUSING : PBT(G.F)UL94V-0
CONTACT: COPPER ALLOY



9-292112-5	15	28	30.8	32
9-4	14	26	28.8	30
9-3	13	24	26.8	28
9-2	12	22	24.8	26
9-1	11	20	22.8	24
9-0	10	18	20.8	22
8-9	9	16	18.8	20
8-8	8	14	16.8	18
8-7	7	12	14.8	16
8-6	6	10	12.8	14
8-5	5	8	10.8	12
8-4	4	6	8.8	10
8-3	3	-AS SHOWN		
8-292112-2	2	-AS SHOWN		
BLACK	POS	A	B	C
PART No.				

TOLERANCES UNLESS OTHERWISE SPECIFIED:
10 $\geq$: ± 0.2
30 $\geq$ * >10 : ± 0.25
100 $\geq$ * >30 : ± 0.3
ANGLE : $\pm 3^\circ$

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm -$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$
MATERIAL SEE NOTE 2	FINISH SEE NOTE 2

DWN J.JIANG 22JAN03	CHK S.YAO 22JAN03	APVD T.SASAKI 22JAN03
PRODUCT SPEC 108-60016		
APPLICATION SPEC 114-5104		
WEIGHT		
CUSTOMER DRAWING		

tyco
Electronics

Tyco Electronics Corporation
Shanghai, China

MT REC HOUSING ASS'Y
(AMP CT CONNECTOR 2mm PITCH)

SIZE A3	CAGE CODE 00779	DRAWING NO C-292112	RESTRICTED TO
SCALE 5:1			SHEET 1 OF 1
			REV A1