



Note:

- 1: Material(材料):
 Barrel: Brass C3604 (针管: 黄铜 C3604)
 Plunger: Brass C3604 (针头: 黄铜 C3604)
 Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀):
 Barrel: 1u' Au over 50~80'u Ni (针管: 镀金3u', 镍底50~80u')
 Plunger: 1u' Au over 50~80'u Ni (针头: 镀金3u', 镍底50~80u')
 Spring: No plated (弹簧: 不电镀)
- 3: Electrical(电气特性):
 Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
 Contact Resistance: 50 mohm Max. at working height.
 接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能):
 Force: 70g±20% at working height. (70g±20% 在工作高度)。
 Durability: 10.000 cycles(min) (寿命: 10000次)
- 5: WorkTemperture(工作环境):
 Withstanding Higt Temperature: 280℃
 Operational Temperature: - 40℃~ + 85℃

NO.	ECN NO.	DESCRIPTION	DATE

深圳市鑫扬泽电子有限公司 TEL:0755-28773277 FAX:0755-28891353		SCALE: N/A	UNIT: mm	THE UNMARKED TOLERANCE ARE AS BELOW : LENGTH ANGLE X.XX ±0.05mm X.XX ±0.50° X.X ±0.10mm X.X ±1.00° X. ±0.20mm X. ±2.00°	DESIGNED BY:	DWG. NO. YZ104313105P-01
		SHEET: 1 of 1	PROJECTION 		CHECKED BY:	TITLE: Pogo pin连接器
		DATE: 2015.07.11	VER.:		APPROVED BY:	