


客户图

NO.	ECN NO.	DESCRIPTION	DATE
-----	---------	-------------	------



Note:

- 1: Material(材料) :
 Barrel: Brass C3604 (针管: 黄铜 C3604)
 Plunger: Brass C3604 (针头: 黄铜 C3604)
 Spring: SUS304 (弹簧: SUS304)
 Plating(电镀) :
 Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)
 Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
 Spring: Gold flash (弹簧: 镀金)
- 2: Electrical(电气特性) :
 Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
 Contact Resistance: 50 mohm Max. at working height.
 接触电阻: 最大50毫欧 (在工作高度状态下)
- 3: Mechanical(机械性能) :
 Force: 50g±20% at working height. (50g±20% 在工作高度)。
 Durability: 10,000 cycles(min) (寿命: 10000次)
- 4: WorkTemperature(工作环境):
 Withstanding Higt Temperature: 280℃
 Operational Temperature: -20℃~ +70℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
 TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	1st Angle
DATE:	2026.04.11	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :
 LENGTH: XXX ±0.05mm, XXX ±0.10mm, XXX ±0.20mm
 ANGLE: XXX ±0.50°, XXX ±1.00°, X ±2.00°

DESIGNED BY:	DWG. NO.	YZ01715085R-04
CHECKED BY:	TITLE:	Pogo pin
APPROVED BY:		