


# 客户图



## Note:

- 1: Material(材料) :  
 Barrel: Brass C3604 (针管: 黄铜 C3604)  
 Plunger: Brass C3604 (针头: 黄铜 C3604)  
 Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀) :  
 Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'. )  
 Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'. )  
 Spring: No flash (弹簧: 不电镀)
- 3: Electrical(电气特性) :  
 Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)  
 Contact Resistance: 50 mohm Max. at working height.  
 接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能) :  
 Force: 30g±20% at working height. (30g±20% 在工作高度)。  
 Durability: 10.000 cycles(min) (寿命: 10000次)
- 5: WorkTemperature(工作环境):  
 Withstanding Higt Temperature: 280<sup>o</sup>  
 Operational Temperature: -20<sup>o</sup>~ +70<sup>o</sup>

| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|
| 1   |         |             |      |

深圳市鑫探技术有限公司  
 HTTP://WWW.XYZPOGOPIN.COM  
 TEL: 0755-28773277 FAX: 0755-28891353



|        |            |            |     |
|--------|------------|------------|-----|
| SCALE: | N/A        | UNIT       | mm  |
| SHEET: | 1 of 1     | PROJECTION | 第一角 |
| DATE:  | 2026.04.11 | VER.       | A-1 |

|                                       |            |
|---------------------------------------|------------|
| THE UNMARKED TOLERANCE ARE AS BELOW : |            |
| LENGTH                                | ANGLE      |
| XXX ±0.05mm                           | XXX ±0.50° |
| X.X ±0.10mm                           | X.X ±1.00° |
| X. ±0.20mm                            | X. ±2.00°  |

|              |          |                |
|--------------|----------|----------------|
| DESIGNED BY: | DWG. NO. | YZ00315035R-10 |
| CHECKED BY:  | TITLE:   | Pogo Pin       |
| APPROVED BY: |          |                |