


客户图

| | | | |
|-----|---------|-------------|------|
| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|



- Note:
- 1: Material(材料): Brass C3604 (黄铜 C3604)
 - 2: Plating(电镀): 3u' Au over 50~80u' Ni(镀金3u', 镍底50~80u'。)

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353



| | | | | | | | | |
|--------|------------|------------|-----------|---------------------------------------|--------|--------------|----------|------------------|
| SCALE: | N/A | UNIT | mm | THE UNMARKED TOLERANCE ARE AS BELOW : | | DESIGNED BY: | DWG. NO. | YZ120120037TP-G3 |
| SHEET: | 1 of 1 | PROJECTION | 1st Angle | LENGTH | ANGLE | CHECKED BY: | TITLE: | Pogo pin 连接器 |
| DATE: | 2026.04.11 | VER. | D.0 | ±0.05mm | ±0.50° | APPROVED BY: | | |
| | | | | ±0.10mm | ±1.00° | | | |
| | | | | ±0.20mm | ±2.00° | | | |