



客户图

NO.	ECN NO.	DESCRIPTION	DATE
1			



Note:

- 1: Material (材料) :
 Barrel: Brass C3604 (针管: 黄铜 C3604)
 Plunger: Brass C3604 (针头: 黄铜 C3604)
 Spring: SUS304 (弹簧: SUS304)
- 2: Plating (电镀) :
 Barrel: 3u' Au over 50~80u' Ni (针管: 镀金3u', 镍底50~80u'.)
 Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
 Spring: Gold flash (弹簧: 镀金)
- 3: Electrical (电气特性) :
 Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
 Contact Resistance: 50 mohm Max. at working height.
 接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical (机械性能) :
 Force: 130g±20% at working height. (130g±20% 在工作高度)
 Durability: 10.000 cycles (min) (寿命: 10000次)
- 5: Work Temperature (工作环境) :
 Withstanding Higt Temperature: 280v
 Operational Temperature: -20v~ +70v

深圳市鑫探技术有限公司
 HTTP://WWW.XYZPOGOPIN.COM
 TEL: 0755-28773277 FAX: 0755-28891353



SCALE:	N/A	UNIT:	mm	DESIGNED BY:		DWG. NO.:	YZ00215030R-02
SHEET:	1 of 1	PROJECTION:		CHECKED BY:		TITLE:	Pogo Pin
DATE:	2026.04.11	VER.:	A.1	APPROVED BY:			

THE UNMARKED TOLERANCE ARE AS BELOW :
 LENGTH: XXX ±0.05mm, XXX ±0.10mm, X ±0.20mm
 ANGLE: XXX ±0.50°, XXX ±1.00°, X ±2.00°