


NO.	ECN NO.	DESCRIPTION	DATE
1			

# 客户图



### Note:

- Material(材料):  
 Barrel: Stainless steel SUS304 (针管: 不锈钢SUS304)  
 Plunger: Brass C3604 (针头: 黄铜 C3604)  
 Spring: SUS304 (弹簧: SUS304)
- Plating(电镀):  
 Barrel: 3u' Au over 50~80'u Ni (针管: 镀金3u', 镍底50~80u'.)  
 Plunger: 3u' Au over 50~80'u Ni (针头: 镀金3u', 镍底50~80u'.)  
 Spring: Gold plated (弹簧: 镀金)
- Electrical(电气特性):  
 Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)  
 Contact Resistance: 100 mohm Max. at working height.  
 接触电阻: 最大100毫欧 (在工作高度状态下)
- Mechanical(机械性能):  
 Force: 100g±20% at working height. (100g±20% 在工作高度)。  
 Durability: 10.000 cycles(min) (寿命: 10000次)
- WorkTemperture(工作环境):  
 Withstanding Higt Temperature: 280°C  
 Operational Temperature: -20°C~ +70°C

深圳市鑫扬泽电子有限公司



HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2023.4.25	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZ145215045R-08
CHECKED BY:		TITLE:	Pogo Pin
APPROVED BY:			