


NO.	ECN NO.	DESCRIPTION	DATE
1			

# 加工图 急



### 技术要求:

- 1.材料: 黄铜 C3604
- 2.不允许有批锋, 毛刺; 切断点最大不超过0.03mm.
- 3.镀金3u', 镍底50~80u'.

深圳市鑫扬泽电子有限公司



HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2016.06.11	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZ136015053T-G3
CHECKED BY:		TITLE:	触点
APPROVED BY:			