



序号	品名	材质
1	端子	磷青铜/表面镀锡
2	焊片	黄铜/表面镀锡
3	基座	LCP UL94V-0 本色
4	锁条	LCP UL94V-0 黑色

技术指标:

1. 额定电流: 0.5A
2. 温度范围: -40~85℃
3. 额定电压: 50V, AC/DC (等效)
4. 接触电阻: ≤0.03Ω
5. 绝缘电阻: ≥500MΩ

Part No	Pin	A	B	C
FPC-0.5AZF2-4PLCR5	4	1.50	2.60	7.60
FPC-0.5AZF2-5PLCR5	5	2.00	3.10	8.10
FPC-0.5AZF2-6PLCR5	6	2.50	3.60	8.60
FPC-0.5AZF2-7PLCR5	7	3.00	4.10	9.10
FPC-0.5AZF2-8PLCR5	8	3.50	4.60	9.60
FPC-0.5AZF2-9PLCR5	9	4.00	5.10	10.10
FPC-0.5AZF2-10PLCR5	10	4.50	5.60	10.60
FPC-0.5AZF2-11PLCR5	11	5.00	6.10	11.10
FPC-0.5AZF2-12PLCR5	12	5.50	6.60	11.60
FPC-0.5AZF2-13PLCR5	13	6.00	7.10	12.10
FPC-0.5AZF2-14PLCR5	14	6.50	7.60	12.60
FPC-0.5AZF2-15PLCR5	15	7.00	8.10	13.10
.....
FPC-0.5AZF2-60PLCR5	60	(60-1)*0.5	(60+1)*0.5+0.1	(60+11)*0.5+0.1

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 0.5-A全包插拔立式(正位)
DECIMALS:	ANGLES:		PAR FPC-0.5AZF2-NPLCR5
X.: ±0.15	±1'		DWN Lucas
X.X: ±0.10			CHKD Ethan
X.XX: ±0.05		APVD Jacob	SCALE 1:1 UNIT: MM
CUSTOMER COPY		SIZE: A4	SHEET: 1F1
			REV: A