


客户图



- Note:
- 1: Material(材料) :
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
 - 2: Plating(电镀) :
Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)
Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
Spring: No plated (弹簧: 不电镀)
 - 3: Electrical(电气特性) :
Rated Current & Voltage: DC 12V,1A (额定电压&电流: 直流12V,1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
 - 4: Mechanical(机械性能) :
Force: 90g±20% at working height. (90g±20% 在工作高度)。
Durability: 10,000 cycles(min) (寿命: 10000次)
 - 5: Work Temperature(工作环境):
Withstanding Higt Temperature: 280°
Operational Temperature: -40°~ +85°

NO.	ECN NO.	DESCRIPTION	DATE

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	第一角
DATE:	2026.04.11	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH	ANGLE		
XXX X.X X.	X.XX X.X X.	±0.05mm ±0.10mm ±0.20mm	±0.5° ±1.0° ±2.0°

DESIGNED BY:	DWG. NO.	YZ116815053D-01
CHECKED BY:	TITLE:	Pogo pin连接器
APPROVED BY:		