



技术指标 (Technical Index):

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
3. 额定电压 (Rated voltage): 50V, AC/DC (=等效).
4. 接触电阻 (Contact resistance): $\leq 0.03\Omega$.
5. 绝缘电阻 (Insulation resistance): $\geq 500M\Omega$.

Number of Contacts	Dimensions mm				
	A	B	C	D	E
4	1.50	2.56	7.60	6.88	
5	2.00	3.06	8.10	7.38	
6	2.50	3.56	8.60	7.88	
7	3.00	4.06	9.10	8.38	
8	3.50	4.56	9.60	8.88	
9	4.00	5.06	10.10	9.38	
10	4.50	5.56	10.60	9.88	
11	5.00	6.06	11.10	10.38	
12	5.50	6.56	11.60	10.88	
13	6.00	7.06	12.10	11.38	
14	6.50	7.56	12.60	11.88	
15	7.00	8.06	13.10	12.38	
16	7.50	8.56	13.60	12.88	
17	8.00	9.06	14.10	13.38	
18	8.50	9.56	14.60	13.88	
19	9.00	10.06	15.10	14.38	
20	9.50	10.56	15.60	14.88	
21	10.00	11.06	16.10	15.38	
22	10.50	11.56	16.60	15.88	
23	11.00	12.06	17.10	16.38	
24	11.50	12.56	17.60	16.88	
25	12.00	13.06	18.10	17.38	
26	12.50	13.56	18.60	17.88	
27	13.00	14.06	19.10	18.38	
28	13.50	14.56	19.60	18.88	
29	14.00	15.06	20.10	19.38	
30	14.50	15.56	20.60	19.88	
31	15.00	16.06	21.10	20.38	
32	15.50	16.56	21.60	20.88	
33	16.00	17.06	22.10	21.38	
34	16.50	17.56	22.60	21.88	
35	17.00	18.06	23.10	22.38	
36	17.50	18.56	23.60	22.88	
37	18.00	19.06	24.10	23.38	
38	18.50	19.56	24.60	23.88	
39	19.00	20.06	25.10	24.38	
40	19.50	20.56	25.60	24.88	
...	
60	29.50	30.56	35.60	34.88	

序号	品名	材质
①	0.5 拉拔3代胶芯 (0E.0) 0.5 Pitch ZIF Type 3 Housing (0#2.0)	LCP UL94V-0 本色 Natural
②	0.5 拉拔立式3代端子 0.5 Pitch ZIF S/T Type 3 terminal	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	0.5 拉拔3代后盖 (0E.0) 0.5 Pitch ZIF Type 3 Actuator (0#2.0)	LCP UL94V-0 黑色 Black
④	0.5 拉拔3代垫片 (0E.0) 0.5 Pitch ZIF Type 3 Fitting Nail (0#2.0)	铜合金/表面镀锡 Copper Alloy/ Tin Plating

序号	变更内容	日期
No.	MODIFY CONTENT	MODIFY DATE
1	初版发行	

GENERAL TOLERANCE		制图	05453	
DIM	TOL	DRAWING	深圳市华灿天禄电子有限公司	
X.X	±0.30 <th>审核</th> <th colspan="2">ShenzhenhuacantianluELECTRONICS CO., LTD</th>	审核	ShenzhenhuacantianluELECTRONICS CO., LTD	
X.XX	±0.20 <th>CHECK</th> <th>产品名称</th> <td>0.5 Pitch 拉拔立式3代</td>	CHECK	产品名称	0.5 Pitch 拉拔立式3代
X.XXX	±0.10 <th>批准</th> <th>TITLE</th> <td>正脚位1代</td>	批准	TITLE	正脚位1代
Angle	±3.0° <th>APPROVAL</th> <th>产品料号</th> <td>HC-FPC-05-LT-NRLTAG</td>	APPROVAL	产品料号	HC-FPC-05-LT-NRLTAG
Projection		SCALE	PART NO.	
		投影	材料	
			MATERIAL	
			版本	REV.
			UNIT	mm
			页次	1/1
			SHEET	