





NO.	ECN NO.	DESCRIPTION	DATE

# 客户图



Note:

- Material(材料):  
Housing: PA46+30%GF (胶芯: PA46)  
Pin: Brass C3604 (针体: 黄铜 C3604)
- Plating(电镀):  
Pin: 3u' Au over 50~80u' Ni(针体: 镀金3u', 镍底50~80u'.)
- Electrical(电气特性):  
Insulation Resistance: 1,000MΩ minimum.  
(绝缘电阻: 1,000MΩ以上)  
Dielectric Withstand Voltage: 500VAC/minute.  
(抗击电压: 500VAC/minute)
- WorkTemperture(工作环境):  
Withstanding Higt Temperature: 280℃  
Operational Temperature: -40℃~ +85℃



RECOMMENDED PCB LAYOUT

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2025.04.03	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.5°
X.X	±0.10mm	X.X	±1.0°
X.	±0.20mm	X.	±2.0°

DESIGNED BY:		DWG. NO.	YZ126715035T-03025-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			