

Features

- Peak power dissipation
200W@10 x 1000 us Pluse
- Low incremental surge resistance
- Excellent clamping capability
- Fast response time
- Low leakage current
- Halogen free and RoHS compliant
- IEC-61000-4-2 ESD
30kV(Air), 30kV (Contact)

Applications

- Personal digital assistants (PDA)
- Cellular handsets & Accessories
- Handhelds and notebooks
- Portable instrumentation


Mechanical Characteristics

- SOD-123FL surface mount package

Dimensions and Pin Configuration



SOD-123FL



Pin Configuration

Maximum Ratings& Thermal Characteristics

(Tamb=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak pulse power (tp=10/1000μs waveform)	P _{PPM}	200	W
Peak pulse power (tp=8/20μs waveform)	P _{PP}	1000	W
ESD voltage (Contact discharge)	V _{ESD}	±30	KV
ESD voltage (Air discharge)	V _{ESD}	±30	KV
Typical thermal resistance junction to ambient	R _{θJA}	220	°C/W
Storage & operating temperature range	T _{STG} ,T _J	-55~+150	°C

Electrical Characteristics (TA=25°C unless otherwise specified)

Type		Marking		V _{RMW}	Breakdown Voltage		Test Current	Reverse Leakage	Max. Clamp Voltage	Peak Pulse Current
					V _{BR} @ I _T		I _T	I _R @ V _{RMW}	V _C @ I _{PP}	I _{PP}
					Min	Max				
Uni	Bi	Uni	Bi	V	V	V	mA	μA	V	A
SJD12A05L01	SJD12C05L01	AE	CAE	5	6.4	7	10	400	9.2	21.7
SJD12A06L01	SJD12C06L01	AG	CAG	6	6.67	7.37	10	400	10.3	19.4
SJD12A6.5L01	SJD12C6.5L01	AK	CAK	6.5	7.22	7.98	10	250	11.2	17.9
SJD12A07L01	SJD12C07L01	AM	CAM	7	7.78	8.6	10	100	12	16.7
SJD12A7.5L01	SJD12C7.5L01	AP	CAP	7.5	8.33	9.21	1	50	12.9	15.5
SJD12A08L01	SJD12C08L01	AR	CAR	8	8.89	9.83	1	25	13.6	14.7
SJD12A8.5L01	SJD12C8.5L01	AT	CAT	8.5	9.44	10.4	1	10	14.4	13.9
SJD12A09L01	SJD12C09L01	AV	CAV	9	10	11.1	1	5	15.4	13
SJD12A10L01	SJD12C10L01	AX	CAX	10	11.1	12.3	1	2.5	17	11.8
SJD12A11L01	SJD12C11L01	AZ	CAZ	11	12.2	13.5	1	2.5	18.2	11
SJD12A12L01	SJD12C12L01	BE	CBE	12	13.3	14.7	1	2.5	19.9	10.1
SJD12A13L01	SJD12C13L01	BG	CBG	13	14.4	15.9	1	1	21.5	9.3
SJD12A14L01	SJD12C14L01	BK	CBK	14	15.6	17.2	1	1	23.2	8.6
SJD12A15L01	SJD12C15L01	BM	CBM	15	16.7	18.5	1	1	24.4	8.2
SJD12A16L01	SJD12C16L01	BP	CBP	16	17.8	19.7	1	1	26	7.7
SJD12A17L01	SJD12C17L01	BR	CBR	17	18.9	20.9	1	1	27.6	7.2
SJD12A18L01	SJD12C18L01	BT	CBT	18	20	22.1	1	1	29.2	6.8
SJD12A20L01	SJD12C20L01	BV	CBV	20	22.2	24.5	1	1	32.4	6.2
SJD12A22L01	SJD12C22L01	BX	CBX	22	24.4	26.9	1	1	35.5	5.6
SJD12A24L01	SJD12C24L01	BZ	CBZ	24	26.7	29.5	1	1	38.9	5.1
SJD12A26L01	SJD12C26L01	CE	CCE	26	28.9	31.9	1	1	42.1	4.8
SJD12A28L01	SJD12C28L01	CG	CCG	28	31.1	34.4	1	1	45.4	4.4
SJD12A30L01	SJD12C30L01	CK	CCK	30	33.3	36.8	1	1	48.4	4.1
SJD12A33L01	SJD12C33L01	CM	CCM	33	36.7	40.6	1	1	53.3	3.8
SJD12A36L01	SJD12C36L01	CP	CCP	36	40	44.2	1	1	58.1	3.4
SJD12A40L01	SJD12C40L01	CR	CCR	40	44.4	49.1	1	1	64.5	3.1
SJD12A43L01	SJD12C43L01	CT	CCT	43	47.8	52.8	1	1	69.4	2.9
SJD12A45L01	SJD12C45L01	CV	CCV	45	50	55.3	1	1	72.7	2.8

Electrical Characteristics (TA=25°C unless otherwise specified)

Type		Marking		V _{RWM}	Breakdown Voltage		Test Current	Reverse Leakage	Max. Clamp Voltage	Peak Pulse Current
					V _{BR} @ I _T		I _T	I _R @ V _{RWM}	V _C @ I _{PP}	I _{PP}
					Min	Max				
Uni	Bi	Uni	Bi	V	V	V	mA	μA	V	A
SJD12A48L01	SJD12C48L01	CX	CCX	48	53.3	58.9	1	1	77.4	2.6
SJD12A51L01	SJD12C51L01	CZ	CCZ	51	56.7	62.7	1	1	82.4	2.4
SJD12A54L01	SJD12C54L01	DE	CDE	54	60	66.3	1	1	87.1	2.3
SJD12A58L01	SJD12C58L01	DG	CDG	58	64.4	71.2	1	1	93.6	2.1
SJD12A60L01	SJD12C60L01	DK	CDK	60	66.7	73.7	1	1	96.8	1.8
SJD12A64L01	SJD12C64L01	DM	CDM	64	71.1	78.6	1	1	103	1.7
SJD12A70L01	SJD12C70L01	DP	CDP	70	77.8	86	1	1	113	1.5
SJD12A75L01	SJD12C75L01	DR	CDR	75	83.3	92.1	1	1	121	1.4
SJD12A78L01	SJD12C78L01	DT	CDT	78	86.7	95.8	1	1	126	1.4
SJD12A85L01	SJD12C85L01	DV	CDV	85	94.4	104	1	1	137	1.3
SJD12A90L01	SJD12C90L01	DX	CDX	90	100	111	1	1	146	1.2
SJD12A100L01	SJD12C100L01	DZ	CDZ	100	111	123	1	1	162	1.1
SJD12A110L01	SJD12C110L01	EE	CEE	110	122	135	1	1	177	1
SJD12A120L01	SJD12C120L01	EG	CEG	120	133	147	1	1	193	0.9
SJD12A130L01	SJD12C130L01	EK	CEK	130	144	159	1	1	209	0.8
SJD12A150L01	SJD12C150L01	EM	CEM	150	167	185	1	1	243	0.7
SJD12A160L01	SJD12C160L01	EP	CEP	160	178	197	1	1	259	0.7
SJD12A170L01	SJD12C170L01	ER	CER	170	189	209	1	1	275	0.6

For bi-directional type having V_{RWM} of 10 Volts and less, the I_R limit is double.

For parts without A, the V_{BR} is +10%.

Typical Characteristics Curves

Figure 1. Peak Pulse Power Rating Curve




Figure 2. Pulse Derating Curve




Figure 3. Pulse Waveform




Figure 4. Typical Junction Capacitance




Figure 5. Steady State Power Dissipation Derating Curve






Figure 6. Maximum Non-Repetitive Forward Surge Current Uni-Directional Only



Recommended Soldering Conditions

Reflow Soldering




Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T_L to T_P)	3°C/second max.
Preheat	
-Temperature Min (T_{Smin})	150°C
-Temperature Max (T_{Smax})	200°C
-Time (min to max) (t_s)	60-180 seconds
T_{Smax} to T_L	
-Ramp-up Rate	3°C/second max.
Time maintained above:	
-Temperature (T_L)	217°C
-Time (t_L)	60-150 seconds
Peak Temperature (T_P)	260°C
Time within 5°C of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

Package Outline Dimensions (unit: mm)

SOD-123FL



Mounting Pad Layout (unit: mm)

