





REV.	Q'TY	ECN. NO.	APR.	DATE





技术要求 Specification:

1. 材质 Material: PA66 UL94V-0;
2. 额定电流 Current rating: 3.0A AC, DC
3. 额定电压 Voltage rating: 250V AC, DC
4. 温度范围 Temperature range: -25℃ to +85℃
5. 接触电阻 Contact resistance: <math><20m\Omega</math>
6. 绝缘电阻 Insulation resistance: >1000M Ω
7. 耐压 Withstand voltage: 1000V AC/minute
8. 塑料表面平整光滑, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



Part No	Pin	A	B	C	D
XY-XH2.54-2P-C	2	2.50	5.70	3.70	3.70
XY-XH2.54-3P-C	3	5.00	8.20	6.20	6.20
XY-XH2.54-4P-C	4	7.50	10.70	8.70	8.70
XY-XH2.54-5P-C	5	10.00	13.20	11.20	11.20
XY-XH2.54-6P-C	6	12.50	15.70	13.70	13.70
XY-XH2.54-7P-C	7	15.00	18.20	16.20	16.20
XY-XH2.54-8P-C	8	17.50	20.70	18.70	18.70
XY-XH2.54-9P-C	9	20.00	23.20	21.20	21.20
XY-XH2.54-10P-C	10	22.50	25.70	23.70	23.70
XY-XH2.54-11P-C	11	25.50	28.20	26.20	26.20
XY-XH2.54-12P-C	12	27.50	30.70	28.70	28.70
XY-XH2.54-13P-C	13	30.00	33.20	31.20	31.20
XY-XH2.54-14P-C	14	32.50	35.70	33.70	33.70
XY-XH2.54-15P-C	15	35.50	38.20	36.20	36.20
XY-XH2.54-16P-C	16	37.50	40.70	38.70	38.70



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecom Electronics Co., Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR. Alex	TITLE: XH2.5MM HOUSING		
.X±0.3	X.*± 5°	CHK. Jack	DWG NO. XY-XH2.54-NP-C		
.XX±0.2	.X.*± 3°	DRA. Can	PROJ.	CUSTOMER DRAWING	
.XXX±0.1	.XX.*± 1°	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A