

1


2

3

4

This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	12/7/06	12/7/06



技术特性/Electrical Specifications

特性阻抗/Impedance
频率范围/Frequency Range
电压驻波比/VSWR
耐压/Withstanding Voltage
绝缘电阻/Insulation Resistance

50 Ω
DC-18GHz
≤1.30
≥1000Vrms
≥5000MΩ

连接参数/The connection parameters

耐久性/durability ≥500次 (cycles)

环境参数/Environmental Data

温度范围/Temperature Range -55℃ to 155℃

材料/Material Data

外导体/Outer contact
中心导体/Center contact
绝缘介质/Insulator
螺套/Nut

黄铜 Brass/金 gold Plated
磷青铜 Phosphor Bronze/金 gold Plated
聚四氟乙烯/PTFE
不锈钢 Stainless Steel/钝化 Passivation

Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 12/07/06

ENGINEER: L.yu 12/07/06

APPROVED: W.yi 12/07/06

TOLERANCES UNLESS OTHERWISE SPECIFIED

X ±0.50
.X ±0.20
.XX ±0.10
ANGLES ±1°

TITLE:

RF Coaxial Connector
RP-SMA Male Conn. For Cable

PART NO: HL3-RPSMA-JB2



DIMENSION IN MILLIMETERS (mm)

SIZE: A4

SCALE: N/A

SHEET: 1/1

REV: A

1

2

3

4