

1



2

3

4

This document contains proprietary information and such information may not be disclosed to others for any purposes,
not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	12/7/06	12/7/06



技术特性/Electrical Specifications

特性阻抗/Impedance	50 Ω
耐压/Withstanding Voltage	≥750V
绝缘电阻/Insulation Resistance	≥5000MΩ

材料/Material Data

外导体/Outer contact	黄铜/Brass/金 gold Plated
中心导体/Center contact	磷青铜/Phosphor Bronze/金 gold Plated
绝缘介质/Insulator	聚四氟乙烯/PTFE

连接参数/The connection parameters

耐久性/durability ≥500次 (cycles)

环境参数/Environmental Data

温度范围/Temperature Range -55℃ to 155℃

Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 12/07/06

ENGINEER: L.yu 12/07/06

APPROVED: W.yi 12/07/06

TOLERANCES UNLESS OTHERWISE SPECIFIED

X ±0.50

.X ±0.20

.XX ±0.10

ANGLES ±1°

TITLE:

Connector

PART NO: HL3-M5-KWHD



DIMENSION IN MILLIMETERS (mm)

SIZE: A4

SCALE: N/A

SHEET: 1/1

REV: A