

1


2

3

4

This document contains proprietary information and such information may not be disclosed to others for any purposes,
not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	12/7/06	12/7/06



技术特性/Electrical Specifications

特性阻抗/Impedance
频率范围/Frequency Range
电压驻波比/VSWR
耐压/Withstanding Voltage
绝缘电阻/Insulation Resistance

50 Ω
DC-18GHz
≤1.20@6GHz
≥500Vrms
≥5000MΩ

连接参数/The connection parameters

耐久性/durability ≥500次 (cycles)

环境参数/Environmental Data

温度范围/Temperature Range -55℃ to 155℃


材料/Material Data

外导体/Outer contact
中心导体/Center contact
绝缘介质/Insulator

黄铜 Brass&铍青铜 Beryllium Copper/金 gold Plated
铍青铜 Beryllium Copper/金 gold Plated
聚四氟乙烯/PTFE

Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 12/07/06	TITLE: RF Coaxial Connector SSMP Female Conn. Terminal				
ENGINEER: L.yu 12/07/06		 DIMENSION IN MILLIMETERS (mm)			
APPROVED: W.yi 12/07/06		PART NO:	HL3-SSMP-KWB1	SIZE: A4	SCALE: N/A
TOLERANCES UNLESS OTHERWISE SPECIFIED X ±0.50 .X ±0.20 .XX ±0.10 ANGLES ±1°		SHEET:	1/1	REV: A	