







技术指标:

- 1. 额定电流: 0.5A
- 2. 温度范围: -40~85℃
- 3. 额定电压: 50V, AC/DC (等效)
- 4. 接触电阻: $\leq 0.03\Omega$
- 5. 绝缘电阻: $\geq 500M\Omega$

Part No	Pin	A	B	C
ZX-1.0FPC-55H-LZ4P	4	3.00	5.15	11.00
ZX-1.0FPC-55H-LZ5P	5	4.00	6.15	12.00
ZX-1.0FPC-55H-LZ6P	6	5.00	7.15	13.00
ZX-1.0FPC-55H-LZ7P	7	6.00	8.15	14.00
ZX-1.0FPC-55H-LZ8P	8	7.00	9.15	15.00
ZX-1.0FPC-55H-LZ9P	9	8.00	10.15	16.00
ZX-1.0FPC-55H-LZ10P	10	9.00	11.15	17.00
ZX-1.0FPC-55H-LZ11P	11	10.00	12.15	18.00
ZX-1.0FPC-55H-LZ12P	12	11.00	13.15	19.00
.....		...		
ZX-1.0FPC-55H-LZ36P	36	(36-1)*1.0	(36+1)*1.0+0.15	(36+7)*1.0



序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-1.0FPC-55H-LZNP	版本 REV.	A
1	1.0A胶芯	LCP UL94V-0 本色				X.:±0.15	±1°		审核 CHECK	LEO		品名 TITLE	1.0-A拉拔立贴 (H:2.5)	页次 SHEET	1/1
2	1.0A立贴端子	磷青铜/表面镀锡				X.X:±0.10				核准 APPROVAL	JOHN		客户料号 CUTM.NO.		
3	1.0A锁条	LCP UL94V-0 黑色				X.XX:±0.05							兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.		
4	1.0A焊片	黄铜/表面镀锡						单位 UNITS	MM	比例 SCALE	1:1				