






序号	品名	材质
1	基座	LCP UL94V-0 本色
2	端子	磷青铜/表面镀锡



Part No	Pin	A	B	C
ZX-1.0FPC-47H-SZ4P	4	3.00	5.10	6.00
ZX-1.0FPC-47H-SZ5P	5	4.00	6.10	7.00
ZX-1.0FPC-47H-SZ6P	6	5.00	7.10	8.00
ZX-1.0FPC-47H-SZ7P	7	6.00	8.10	9.00
ZX-1.0FPC-47H-SZ8P	8	7.00	9.10	10.00
ZX-1.0FPC-47H-SZ9P	9	8.00	10.10	11.00
ZX-1.0FPC-47H-SZ10P	10	9.00	11.10	12.00
ZX-1.0FPC-47H-SZ11P	11	10.00	12.10	13.00
ZX-1.0FPC-47H-SZ12P	12	11.00	13.10	14.00
.....		...		
ZX-1.0FPC-47H-SZ36P	36	(36-1)*1.0	(36+1)*1.0+0.10	38.00

- 技术指标:
- 1.额定电流:0.5A
 - 2.温度范围:-40~85℃
 - 3.额定电压:50V,AC/DC (等效)
 - 4.接触电阻:≤0.03Ω
 - 5.绝缘电阻:≥500MΩ

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-1.0FPC-47H-SZNP	版本 REV.	A
			X.:±0.15	±1°	审核 CHECK	LEO			品名 TITLE	1.0B黑色双面接立式 (正位)	页次 SHEET	1/1
			X.X:±0.10		核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			X.XX:±0.05									
					单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd			