





RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE



SECTION A-A
SCALE 1:1



PCB WELDING DRAWING (TOLERANCE: ±0.05)

技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC, DC.

PIN number variable size comparison table


PART NO	PIN	A	B
W420121K-2PW2123	2*1	0.00	5.40
W420121K-4PW2123	2*2	4.20	9.60
W420121K-6PW2123	2*3	8.40	13.80
W420121K-8PW2123	2*4	12.60	18.00
W420121K-10PW2123	2*5	16.80	22.20
.....
W420121K-24PW2123	2*12	46.20	51.60

2	端子 Contact	黄铜	N*1	表面镀锡
1	基座 Wafer	PA66UL94V-2	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	W420121K-XPW2123	4.2MM WAFER DIP TYPE
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	
		APPD: Sophia	UNITS MM
			SCALE
			SHEET
			N:A
			1/2

RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	PART NO. W420121K-XPB2123		TITLE: 4.2MM WAFER DIP TYPE	
X.X ±0.30	X.° ±5°		DESIGN: <i>James</i>	CUSTOMER	SIZE	UNITS
.XX ±0.20	X.X° ±1°	CHED: <i>Talen</i>	A4		MM	
.XXX ±0.10	X.XX° ±0.5°	APPD: <i>Sophia</i>		SCALE	SHEET	
MANUFACTURE DWG		N:A		2/2		